


Portable **40** cells Braille display with note taking capability,

Ergonomic control layout Affordable Braille Notetaker



NEW

清華

Braille Display

Seika

version **6 Pro**

Seika v6Pro is compatible with several popular screen reading software. It works well in conjunction with a mobile phone and PC via Bluetooth or USB cable.

User friendly Function keys with Precise and efficient features allow the user to navigate the Braille display naturally allowing for a more comfortable user experience.



Specification:

Display system	8 dots Braille
Display capacity	40 cells
Keyboard	8-dots Braille keyboard 8 function keys 40 cursor routing keys 2 Navigation joysticks keys
Memory extension	Micro SD Card and U-disk
Wireless	Bluetooth
Interface	USB, MiniUSB, Micro SD card slot, DCIN
Power supply	Bus power/AC adapter/Battery
Long-life Battery	•Lasts up to 10 hours with Bluetooth •Recharges from the USB port and DCIN •Auto-shut off •Lithium-ion rechargeable battery •Compatible with any standard USB A/C adapter
Size / Weight	330(W)x11(D)x38(H)mm / 680g

Compatible software:

* Jaws * Window-Eyes
* NVDA * Talks * MobileSpeak * Talkback for Android
* VoiceOver (Apple Mac and iOS)

**TELE
SOFT**

NIPPON TELESOFT Co.,Ltd.

E-mail: ts-info@telesoft.co.jp


<http://www.nippontelesoft.com>

New product

清華 Braille Display

Seika
version 6
SUPER

Braille and **speech in English**
simultaneously !



You might prefer the Braille display when editing or reading detailed material during meetings but prefer speech for reading longer documents such as novels when reading for pleasure.

Seika6 Super can output Braille and also speech in English. When text is entered using English language, the language attribute is attached to that text. you can choose to read using Braille only or speech only. You can also use both Braille and speech simultaneously.

Seika6 Super can speak menu, hints, and messages. When you edit or read text, it can also speak whole document, selected Text, current sentence, current word, current character. You can control the volume and speed of the speech on Seika6 Super.

You can listen to the Seika6 Super using either the built-in loudspeaker or headphones. If headphones are plugged in, the loudspeaker is automatically disabled.

TELE
SOFT

NIPPON TELESOFT Co.,Ltd.

E-mail: ts-info@telesoft.co.jp

<http://www.nippontelesoft.com>